


# Suitable formats – individually or in combination

Zehnder Fleximo activation modules are available in three widths and seven lengths. Combining two or more activation modules in one cassette allows metal cassettes of any size or shape to be activated – even with cut-outs or additional components. Flexible hoses are used for connecting the activation modules to each other, as well as for the connection to the pipework.


## Zehnder Fleximo

Activation module width 350 mm with 2 parallel pipes, pitch 175 mm



## Zehnder Fleximo

Activation module width 550 mm with 4 parallel pipes, pitch 138 mm



## Zehnder Fleximo

Activation module width 900 mm with 6 parallel pipes, pitch 150 mm

